

For a single ended input, short the "-" input to gnd



This symbol is a current source, shown in detail in drawing 2


Overall gain will be 20dB with the 'between the cathodes' trimmer set at 180R for single ended input – or 350R for differential input

PP-2C Triode Connection
© 2004 by Allen Wright/VSE


Drw 1 of 2

Scale:

VACUUM STATE ELECTRONICS



Current Sources for input tubes



All resistors are 1 watt metal film 1% unless otherwise marked. Non-magnetic preferred.
Except 100Ω which are 1/4 watt metal film 1%

PP-2C Triode Connection

© 2004 by Allen Wright/VSE

Drw 2 of 2

Scale:

VACUUM STATE ELECTRONICS